

Polypropylene, Random Copolymer

**Product Description**

*Purell RP373R* is a polypropylene random copolymer for usage in injection molding applications.

*Purell RP373R* contains a slip agent and exhibits good transparency.

*Purell RP373R* is designed for empty disposable two-part syringes.

All potential activities for applications in the pharmaceutical, medical device, laboratory and diagnostics area have to be discussed with the relevant Technical and Business contacts first. To discuss a medical/pharmaceutical application please contact your local Lyondellbasell reference or your local Distributor.

**Regulatory Status**

For regulatory compliance information, see *Purell RP373R* [Product Stewardship Bulletin \(PSB\) and Safety Data Sheet \(SDS\)](#).

<b>Status</b>	Commercial: Active
<b>Availability</b>	Africa-Middle East; Asia-Pacific; Australia and New Zealand; Europe; North America; South & Central America
<b>Application</b>	Healthcare Applications; Syringes
<b>Market</b>	Healthcare
<b>Processing Method</b>	Injection Molding
<b>Attribute</b>	Autoclavable; Ethylene Oxide Sterilisation; Good Optical Properties; Medium Flow; Medium Slip; Random Copolymer

Typical Properties	Nominal Value	Units	Test Method
<b>Physical</b>			
Melt Flow Rate, (230 °C/2.16 kg)	25	g/10 min	ISO 1133-1
Density, (23 °C)	0.90	g/cm <sup>3</sup>	ISO 1183-1
<b>Mechanical</b>			
Tensile Modulus	1000	MPa	ISO 527-1, -2
Tensile Stress at Yield	27	MPa	ISO 527-1, -2
Tensile Strain at Break	>50	%	ISO 527-1, -2
Tensile Strain at Yield	15	%	ISO 527-1, -2
<b>Impact</b>			
Charpy Impact Strength - Notched			
(23 °C, Type 1, Edgewise, Notch A)	6.0	kJ/m <sup>2</sup>	ISO 179
(0 °C)	2.5	kJ/m <sup>2</sup>	ISO 179
<b>Hardness</b>			
Ball Indentation Hardness, (H 358/30)	45	MPa	ISO 2039-1
<b>Thermal</b>			
Vicat Softening Temperature, (A50)	130	°C	ISO 306
Heat Deflection Temperature B, (0.45 MPa, Unannealed)	72	°C	ISO 75B-1, -2
<b>Optical</b>			
Haze, (1 mm - injection molded disc)	9	%	ASTM D1003

## Notes

These are typical property values not to be construed as specification limits.

## Further Information

### Health and Safety:

The resin is manufactured to the highest standards, but special requirements apply to certain applications such as food end-use contact and direct medical use. For specific information on regulatory compliance contact your local representative.

Workers should be protected from the possibility of skin or eye contact with molten polymer. Safety glasses are suggested as a minimal precaution to prevent mechanical or thermal injury to the eyes.

Molten polymer may be degraded if it is exposed to air during any of the processing and off-line operations. The products of degradation may have an unpleasant odor. In higher concentrations they may cause irritation of the mucus membranes. Fabrication areas should be ventilated to carry away fumes or vapours. Legislation on the control of emissions and pollution prevention should be observed.

The resin will burn when supplied with excess heat and oxygen. It should be handled and stored away from contact with direct flames and/or ignition sources. While burning, the resin contributes high heat and may generate a dense black smoke.

Recycled resins may have previously been used as packaging for, or may have otherwise been in contact with, hazardous goods. Converters are responsible for taking all necessary precautions to ensure that recycled resins are safe for continued use.

For further information about safety in handling and processing please refer to the Safety Data Sheet.

### Conveying:

Conveying equipment should be designed to prevent production and accumulation of fines and dust particles that are contained in polymer resins. These particles can under certain conditions pose an explosion hazard. Conveying systems should be grounded, equipped with adequate filters and regularly inspected for leaks.

### Storage:

The resin is packed in 25 kg bags, octabins or bulk containers protecting it from contamination. If it is stored under certain conditions, i. e. if there are large fluctuations in ambient temperature and the atmospheric humidity is high, moisture may condense inside the packaging. Under these circumstances, it is recommended to dry the resin before use. Unfavorable storage conditions may also intensify the resin's slight characteristic odor.

Resin should be protected from direct sunlight, temperatures above 40°C and high atmospheric humidity during storage. Higher storage temperatures may reduce the storage time.

The information submitted is based on our current knowledge and experience. In view of the many factors that may affect processing and application, these data do not relieve processors of the responsibility of carrying out their own tests and experiments; neither do they imply any legally binding assurance of certain properties or of suitability for a specific purpose. This information does not remove the obligation of the customer to inspect the material on arrival and notify us of any faults immediately. It is the responsibility of those to whom we supply our products to ensure that any proprietary rights and existing laws and legislation are observed.

## Company Information

For further information regarding the LyondellBasell company, please visit <http://www.lyb.com/>.

© LyondellBasell Industries Holdings, B.V. 2018

## **Disclaimer**

Information in this document is accurate to the best of our knowledge at the date of publication. The document is designed to provide users general information for safe handling, use, processing, storage, transportation, disposal and release and does not constitute any warranty or quality specification, either express or implied, including any warranty of merchantability or fitness for any particular purpose. Users shall determine whether the product is suitable for their use and can be used safely and legally.

In addition to any prohibitions of use specifically noted in this document, LyondellBasell may further prohibit or restrict the sale of its products into certain applications. For further information, please contact a LyondellBasell representative.

## **Trademarks**

The Trademark referenced within the product name is owned or used by the LyondellBasell family of companies.